

[See all 76 Products in Family](#)

LightPath 354453 | 6mm Dia., 0.55 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-158** **20+ In Stock**

[Other Coating Options](#)

-

1

+

€75⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€75,00 each
Qty 11-49	€67,50 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Thickness: 0.28 (t) (mm) Material: BK7	Compatible Window:
354453	Lightpath Lens Code:
Aspheric Lens	Type:

Typical Applications:	
Collimate or Focus Laser Light	
Physical & Mechanical Properties	
Diameter (mm):	6.00 ±0.020
Clear Aperture CA (mm):	4.8
Edge Thickness ET (mm):	1.75
Center Thickness CT (mm):	3.14 ±0.02
Bevel:	Protective as needed
Distance from Window to Lens (D) (mm):	2.049
Optical Properties	
Effective Focal Length EFL (mm):	4.60 @ 655nm
Numerical Aperture NA:	0.55
Substrate: ☐	D-ZK3
Focal Length Tolerance (%):	±1
Aspheric Design Wavelength (nm):	655
Coating:	BBAR (600-1050nm)
Coating Specification:	R _{abs} <1.0% @ 600 - 1050nm
Surface Quality:	40-20
f/#:	0.91
Wavelength Range (nm):	600 - 1050
Working Distance (mm):	2.7
Conjugate Distance:	Infinite
Transmitted Wavefront Error (λ, RMS):	< 0.09
Environmental & Durability Factors	
Operating Temperature (°C):	≤200
Regulatory Compliance	
RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 247:	Compliant

Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



Compatible Mounts

;