

[See all 8 Products in Family](#)

0.19 - 20 μ m, 110W, Thermopile Power & Energy Detector



0.19 - 20 μ m, 110W, Thermopile Power & Energy Detector

Stock #78-465 **NEW** 1 In Stock

⊖ 1 ⊕ €2.200⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€2.200,00 each
Qty 5+	€1.980,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Maximum Incident Energy Density (J/cm², 10ns Pulses):

1

General

UP19k-100F-H9-INT-D0 (US)

Model Number:

Fan Cooled

Cooling Method:

Compatible Meters:

Physical & Mechanical Properties54.2 x 54.2 x 55.6 **Dimensions (mm):**160 **Weight (g):**0.16 **Weight (kg):**19 **Active Area (mm):****Optical Properties**190 - 20000 **Wavelength Range (nm):**0.19 - 20 **Wavelength Range (μm):****Sensor**Thermopile **Type of Sensor:****Electrical**110,000 **Maximum Incident Beam Power (mW):**110 **Maximum Incident Beam Power (W):**45,000 **Maximum Incident Power Density (W/cm²):**45 **Maximum Incident Power Density (kW/cm²):**3 mW **Noise Level:****Regulatory Compliance**[View](#) **Certificate of Conformance:****Product Details**

- Photodetectors, Thermopiles, and Pyroelectric Detectors Available
- Various Active Area Sizes Across a Wide Range of Sensitivities
- [Meterless](#) and [Wireless](#) Detectors Also Available

Gentec-EO Integra USB Power and Energy Detectors combine a power meter and detector in one convenient package while providing fast response times and accurate measurements for beam analysis. These detectors are designed with a USB connector for easy connection to a PC or other acquisition system and include user-friendly software allowing for control via PC or serial commands. Versatile pyroelectric energy detectors with broadband coatings are optimized for low to high power densities. Gentec-EO Integra USB Power and Energy Detectors can be used with a variety of laser powers ranging from the nanowatts to multi-kilowatts. These detectors are ideal for laser energy measurement, thermal imaging, and remote sensing applications.