

TECHSPEC® 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens



110mm WD, 0.75X, In-Line Version (Left) and MS Version (Right)



Stock #67-304 **12 In Stock**

- 1 + €1.065⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€1.065,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

CompactTL™ Series

Product Family:

Edmund Optics®

Manufacturer:

Telecentric Lens

Type:

Compatible Light Guide/Source:
1/4" (0.312") and 1/8" (0.187")

Type of Illumination:
In-Line Illumination

Physical & Mechanical Properties

Fixed Iris Option:

160.01 Length (mm):

160.01 Length excluding Threads (mm):

29.5 Maximum Diameter (mm):

120 Weight (g):

Optical Properties

11.7mm Horizontal Field of View, 2/3" Sensor:

8.5mm Horizontal Field of View, 1/2" Sensor:

6.4mm Horizontal Field of View, 1/3" Sensor:

11.00 Maximum Image Circle (mm):

0.028 Numerical Aperture NA, Object Side:

±1 Working Distance Tolerance (mm):

5 (5) Number of Elements (Groups):

0.061 Typical Telecentricity @ 588nm (°):

0.0212 Typical Distortion @ 588nm (%):

0.75X Primary Magnification PMAG:

0.75 Telecentric Lens Magnification:

110 Working Distance (mm):

11.7 x 8.8 FOV @ Max Sensor Format, H x V (mm):

f/13.3 Aperture (f/#):

N4 MgF₂ Coating:

±1.2mm (20% @ 20 lp/mm) Depth of Field (mm):

0.75X Magnification:

VS Lens Wavelength Range:

Sensor

2/3" Maximum Sensor Format:

4.50 Pixel Size (µm):

Threading & Mounting

M25.5 x 0.50 (Female) Filter Thread:

C-Mount Mount:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:


REACH 241:

Product Details


- 2/3", C-Mount Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Small Telecentric Lens with Coaxial Illumination Options

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion. The fixed iris and lockable focus make these lenses ideal for implementation into factory floors and assembly lines, as they will remain fixed over time.


Technical Information




#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Distortion Plot




#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Relative Illumination Plot



#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Telecentricity Plot



#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Modulated Transfer Function (MTF) Plot, 110mm Working Distance, f13.3



#67-304, 0.75X, 110mm WD, In-Line CompactTL™ Telecentric Lens, Depth of Field Plot, 110mm Working Distance, f13.3