

0.30 NA, 8.0mm FL, HOYA Molded Glass Aspheric Lens

See More by [Hoya](#)



HOYA Molded Glass Aspheric Lenses

Stock **#13-583** ☒ In Stock

-

1

+

€95,00

ADD TO CART

Qty 1-10

€95,00

Qty 11+

€75,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
6.37 +0.00/-0.02

Effective Focal Length EFL (mm):
8.00 @ 780nm

Numerical Aperture NA:
0.30

Substrate: M-BaCD5N
Aspheric Design Wavelength (nm): 780
Coating: BBAR (680-880nm)
Coating Specification: R_{avg} <1% @ 680 - 880nm (typical)
Center Thickness CT (mm): 4.00
f/#: 1.26
Bevel: Protective bevel as needed
Type: Aspheric Lens
Wavelength Range (nm): 680 - 880
Working Distance (mm): 5.52
Conjugate Distance: 0
Transmitted Wavefront, RMS @ 632.8nm: 0.04λ
Model Number: A63_Z

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View