


TECHSPEC[®] 0° AOI, 20.0mm Square, Cold Mirror



TECHSPEC High Performance Cold Mirrors

Stock **#64-436** **4 In Stock**

-

1

+

€25⁰⁰ €50,99

ADD TO CART

Volume Pricing	
Qty 1-9	€50,99 €25,50 each
Qty 10-25	€45,84 €22,92 each
Qty 26-49	€43,52 €21,76 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Cold Mirror

Type:


Physical & Mechanical Properties	
20.0 x20.0	Dimensions (mm):
1.10 ±0.2	Thickness (mm):
+0.0/-0.2	Dimensional Tolerance (mm):
Optical Properties	
0	Angle of Incidence (°):
Cold Mirror, 0°	Coating:
BOROFLOAT®	Substrate: ☐
80-50	Surface Quality:
Longpass Filter	Transmission (%):
Coating Specification: R _{avg} ≥95% @ 400 - 690nm and T _{avg} ≥90% @ 750 - 1200nm AR Coating: R _{avg} <1% @ 700 - 1150nm	
400 - 1150	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):
Dielectric	Coating Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- >95% Reflection from 400 - 690nm
- >90% Transmission from 750 - 1200nm
- Optimized for 0° or 45° Angle of Incidence

TECHSPEC® High Performance Cold Mirrors feature a multi-layer dielectric coating optimized for greater than 95% reflection of visible light and greater than 90% transmission of IR wavelengths. Cold mirrors are designed for use in any application where heat build-up can cause damage or adverse effects. For high power illumination, forced air cooling is recommended.

TECHNICAL INFORMATION



COMPATIBLE MOUNTS

