

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #15-873 [CONTACT US](#)



1



€2.995,00

ADD TO CART

Qty 1+

€2.995,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
175.00

Horizontal Field of View, 1/2" Sensor:
11.59mm

Horizontal Field of View, 2/3" Sensor:
15.93mm

Filter Thread:
M52 x0.75 (Female)

Maximum Diameter (mm): 55
Weight (g): 792.4
Horizontal Field of View, 1" Sensor: 23.17mm
Maximum Image Circle (mm): 17.60
Numerical Aperture NA, Object Side: 0.058
Stock No. of Mounting Clamp: #63-233 - Sold Separately
Horizontal Field of View, 1.1" Sensor: 20.39mm
Number of Elements (Groups): 9 (7)
Note: CobaltTL
Horizontal Field of View, 1/1.8" Sensor: 13.04mm
Type: Telecentric Lens
Primary Magnification PMAG: 0.69X
Maximum Sensor Format: 1.1"
Working Distance (mm): 110
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/4.5 - f/22
Coating: λ/4 MgF ₂
Depth of Field (mm): ±2.16mm at f/10 (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 20.4 x 15.3
Typical Distortion @ 520nm (%): <0.027
Typical Telecentricity @ 520nm (°): <0.086
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View