

[See all 29 Products in Family](#)

0.75" Travel, Fine Screw, Solid-Top Ball Bearing Stage



2.62" Center drive stage and its X-Y configuration

Stock **#37-978** [CONTACT US](#)

1 €680⁰⁰

[ADD TO CART](#)

Volume Pricing

Qty 1+	€680,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

English	Type:
Solid Top	Note:

Physical & Mechanical Properties

Linear (X) Type of Movement:

Ball Bearing Guide System:

Center Drive Drive Orientation:

66.5 x 66.5 Stage Size (mm):

0.75 Travel (inches):

Aluminium Stage Construction:

0.001 Graduation (inches):

1.00 Height (inches):

25.4 Height (mm):

62 Load Capacity, Normal (lbs):

2.62 x 2.62 Stage Size (inches):

0.00008/inch of travel Straight Line Accuracy (inches):

0.72 Weight (lbs):

10 Thrust Capacity, T_a (lbs):

2 Thrust Capacity, T_b (lbs):

Hardware & Interface Connectivity

Fine Screw (64 Pitch) Type of Drive:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Product Details

[Adapter Plates](#) and [Z-Axis Brackets](#) are available for ball bearing stages and slides.

- Preloaded Ball Bearing Design for Low-Friction Linear Adjustment
- Solid-Top and Thru-Hole Versions
- English or Metric Micrometer Drive and Fine Screw Drive Available
- Stackable for 2-Axis or 3-Axis Movement

English Ball Bearing Translation Stages with an English hole pattern on both the top and bottom plates have a preloaded ball bearing design that offers straight line accuracy of 0.00008inch per inch of travel. These stages are available in a variety of stage sizes with multiple options of drive orientation, travel distance, and drive mechanism, as well as top plates with or without a clearance thru-hole. The English and Metric micrometer models offer graduations of 0.001inch or 0.01mm for applications that require a position readout while the Fine Screw (64 Pitch) models offer fine resolution positioning. English Ball Bearing Translation Stages are designed to have low friction, providing smooth linear motion without backlash or sideplay. All stages include screws for creating an X-Y stage and a position lock.

Note: [Adapter Plates](#) and [Z-Axis Brackets](#) are available for breadboard mounting application and X-Y-Z configuration. Brackets include screws for assembling X-Y-Z stages from multiple stages.