

TECHSPEC® 1000 - 1060nm, 50.8mm Dia., Ultrafast Mirror



Stock #14-847 3-4 DAYS

⊖ 1 ⊕ **€519,00**

ADD TO CART

Qty 1-9
€519,00

Qty 10+
€458,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality: 10-5
Type: Laser Mirror
Typical Applications: Yb:doped Lasers 1st Harmonic

Clear Aperture (%): 80
Back Surface: Commercial Polish
Coating Specification: Rs >99.95% @ 1000 - 1060nm Rp >99.9% @ 1000 - 1060nm
GDD Specification: 0 ±20fs² @ 1000 - 1060nm (s-pol & p-pol)
Wavelength Range (nm): 1000 - 1060
Surface Flatness (P-V): λ/8
Coating Type: Dielectric
Coating: Ultrafast (1000-1060nm)
Design Wavelength DWL (nm): 1030
Diameter (mm): 50.80 +0.00/-0.10
Thickness (mm): 9.52 ±0.10
Angle of Incidence (°): 45
Substrate: ☐ Fused Silica (Corning 7980)
Parallelism (arcsec): <10
Damage Threshold, By Design: ☐ 0.45 J/cm² @ 1030nm, 207fs, 1 pulse 0.35 J/cm² @ 1030nm, 207fs, 1,000 pulses

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View