


TECHSPEC<sup>®</sup> 1" Dia, 8" FL 320-450nm, Spherical Mirror



Stock **#72-965** [CONTACT US](#)

-

1

+

€175<sup>10</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €175,10 each                  |
| Qty 6+         | €139,05 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Spherical MirrorType:

| Physical & Mechanical Properties                                                                                                                                                                                   |                                                       |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| 25.40 +0/-0.3                                                                                                                                                                                                      | Diameter (mm):                                        |
| Ground                                                                                                                                                                                                             | Back Surface:                                         |
| 1.0                                                                                                                                                                                                                | Diameter (inches):                                    |
| +0/-0.01                                                                                                                                                                                                           | Diameter Tolerance (inches):                          |
| 0.25                                                                                                                                                                                                               | Edge Thickness ET (inches):                           |
| 6.35                                                                                                                                                                                                               | Edge Thickness ET (mm):                               |
| +0.0/-15                                                                                                                                                                                                           | Edge Thickness Tolerance (%):                         |
| Optical Properties                                                                                                                                                                                                 |                                                       |
| Dielectric                                                                                                                                                                                                         | Coating Type:                                         |
| Dielectric Mirror (320-450nm)                                                                                                                                                                                      | Coating:                                              |
| 320 - 450                                                                                                                                                                                                          | Wavelength Range (nm):                                |
| 203.20                                                                                                                                                                                                             | Effective Focal Length EFL (mm):                      |
| BOROFLOAT®                                                                                                                                                                                                         | Substrate: <input type="checkbox"/>                   |
| f/8                                                                                                                                                                                                                | Aperture (f/#):                                       |
| Coating Specification:<br>R <sub>avg</sub> >98% @ 340 - 488nm (0°, All Polarizations)<br>R <sub>avg</sub> >98% @ 320 - 450nm (45°, All Polarizations)<br>R <sub>avg</sub> >99% @ 320 - 450nm (45°, S-Polarization) |                                                       |
| 8.00                                                                                                                                                                                                               | Effective Focal Length EFL (inches):                  |
| ±2                                                                                                                                                                                                                 | Focal Length Tolerance (%):                           |
| λ/4                                                                                                                                                                                                                | Surface Accuracy:                                     |
| 60-40                                                                                                                                                                                                              | Surface Quality:                                      |
| 0.5 J/cm² @ 355nm, 20ns, 20Hz                                                                                                                                                                                      | Damage Threshold, By Design: <input type="checkbox"/> |
| Regulatory Compliance                                                                                                                                                                                              |                                                       |
| <a href="#">View</a>                                                                                                                                                                                               | Certificate of Conformance:                           |

## PRODUCT DETAILS

- Ideal for Multispectral Focusing Applications
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Multiple Sizes Available

TECHSPEC® Broadband Dielectric Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. A BOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® Broadband Dielectric Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors collect and focus light without introducing chromatic aberration.

## TECHNICAL INFORMATION

