

Norland Optical Adhesive NOA 1665, 1 oz. Application Bottle

See More by [Norland](#)



1 oz. Application Bottle of NOA (NOA60 shown as an example)



Stock **#12-863** [CONTACT US](#)

⊖ 1 ⊕ **€115,50**

ADD TO CART

Qty 1-4

€115,50

Qty 5+

€109,80

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):
1

Glass Bonding:
Excellent

Metal Bonding: Good
Plastic Bonding: Excellent
Viscosity (cps): 800 - 1000
Durability: Flexible
Index of Refraction n_d: 1.665 @ 589nm
Norland Number: 1665
Shelf Life: 4 months
Type: Bottle
Typical Applications: High refractive index adhesive for bonding glass, plastics and metal.
Absorption Range (nm): 315 - 450
Bonding Type: Glass to Glass
Energy for Full Cure (J/cm²): 6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant