

100 x 100mm 120 Grit Ground Glass Diffuser



Stock #83-384 **5 In Stock**

€52⁵⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | €52,50 each |
| Qty 11+ | €48,50 each |
| Need More? | Request Quote |

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Ground Glass Diffuser **Type:**

Sandblasted on first surface **Note:**

Physical & Mechanical Properties

Dimensional Tolerance (mm):

±0.25

| | |
|-----------------|---------------------------------------|
| 100.00 x 100.00 | Dimensions (mm): |
| Cut | Edges: |
| 120 | Grit: <input type="checkbox"/> |
| 1.60 | Thickness (mm): |
| 100.00 | Width (mm): |
| 100.00 | Length (mm): |

Optical Properties

| | |
|-------------|--|
| Uncoated | Coating: |
| Float Glass | Substrate: <input type="checkbox"/> |
| 350 - 2000 | Wavelength Range (nm): |

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 247: |

Product Details

- Available in Sizes Ranging from 5mm Diameter to 250mm Square
- Low Scatter Loss
- Evenly Ground Surface for Even Diffusion
- [Fused Silica Substrates](#) Available

Ground Glass Diffusers are comprised of high tolerance, quality ground glass making them ideal for a variety of industrial applications. The float glass substrate has excellent visible transmission and is ideal for general diffusing applications. A 120-grit, 220-grit or 600-grit (as noted) sandblast is used to create a diffuse surface on the glass. Ground Glass Diffusers have even diffusion across the entire surface from undergoing two orthogonal passes during this sandblast process. The scattering is a compromise of low scatter loss and medium diffusion. Typical applications include use in screens, illuminator diffusion, and targets.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



[Quote Your Size](#)

[Compatible Mounts](#)