

[See all 13 Products in Family](#)

100X Oil Immersion Objective, CFI Plan Achromatic

See More by [Nikon](#)



Stock #75-358 NEW 1 In Stock

-

1

+

€1.085⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.085,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
MRL01903	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm	
Microscope Objective	Type:
Infinity Corrected	Style:

Nikon	Manufacturer:
Physical & Mechanical Properties	
0.22	Field of View (mm):
59.67	Length excluding Threads (mm):
27.5	Maximum Diameter (mm):
170	Weight (g):
Optical Properties	
0.17	Compatible Cover Glass Thickness (mm):
0.064	Horizontal Field of View, 1/2" Sensor:
0.088	Horizontal Field of View, 2/3" Sensor:
100X	Magnification:
1.25	Numerical Aperture NA:
0.2	Working Distance (mm):
22	Field Number (mm):
59.87	Parfocal Length (mm):
Oil	Immersion Liquid:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M25 x0.75	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Exceptional Flat-Field Imaging
- High Numerical Apertures and Oil Immersion Options Available
- Wide Magnification Range (1Xto 100X)

Nikon's CFI Plan Achromat Objectives deliver exceptional flat-field imaging ensuring sharp, distortion-free clarity across the entire field of view, making these objectives ideal for both visual inspection and high-precision digital imaging. With high numerical apertures and specialized oil immersion options available, these objectives offer enhanced resolution and light-gathering capabilityfor demanding high-magnification applications. Nikon CFI Plan Achromat Objectives are available in 1Xup to 100Xmagnification, providing solutions for low-magnification overviews or detailed high-resolution imaging. Color corrected for the entire visible spectrum; these objectives are suitable for brightfield and fluorescence observation in routine lab work and photomicrography.