

101 x 127mm, Extended Hot Mirror



Extended Hot Mirrors

Stock #47-304 **10 In Stock**

⊖ 1 ⊕ €296.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€296,00 each
Qty 10-25	€266,00 each
Qty 26-49	€253,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Shortpass Filter **Type:**

Physical & Mechanical Properties

101.0 x 127.0 **Dimensions (mm):**

Thickness (mm):

3.30 ±0.2

Dimensional Tolerance (mm):

±0.5

Clear Aperture (%):

≥85

Edges:

Seamed

Optical Properties

Angle of Incidence (°):

0.00

Coating:

Hot Mirror, 0°

Substrate:

BOROFLOAT®

Surface Quality:

80-50

Coating Specification:

R_{avg} ≥90% @ 750 - 1150nm
R_{avg} ≥80% @ 1200 - 1600nm
T_{avg} ≥85% @ 425 - 675nm

Wavelength Range (nm):

425 - 1600

Surface Flatness (P-V):

4 - 6λ

Coating Type:

Dielectric

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant


Product Details

- Improved NIR Reflectance Over Standard Hot Mirrors
- Operating Temperatures up to 230°C
- Neutral Color for 5500K or 3200K Sources to ±250K

Extended Hot Mirrors are designed to reduce the heat in an optical system without sacrificing the system's visible output. While typical hot mirrors reflect from 750nm to approximately 1250nm, Extended Hot Mirrors further reduce heat by extending the reflection range to approximately 1750nm.

Hot mirrors are crucial in many projection and illumination systems where high levels of heat can quickly damage sensitive components. Hot mirrors are specially coated to transmit visible light while reflecting the NIR, a major contributor to heat generation. By using a hot mirror, heat levels are limited with minimum impact on the overall system performance.

Technical Information



Quote Your Size

Compatible Mounts
