

10.6µm, 27.94mm Dia., 1x2 Spot Array, Diffractive Beamsplitter



HOLO/OR Diffractive Beamsplitters

Stock **#14-694** 3-4 DAYS

- 1 + **€2.920,00**

ADD TO CART

Qty 1+
€2.920,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
25.1

Coating:
Laser V-Coat (10.6µm)

Design Wavelength DWL (nm):
10600

Diameter (mm):
27.94 +0.05/-0.15

Substrate:

Zinc Selenide (ZnSe)
Thickness (mm): 3.00 ±0.1
Input Beam Mode: SMor MM
Minimum Beam Diameter (mm): 1.35
Overall Efficiency (%): 79
Full Angle (°) : 2.70
Output Number of Spots: 2
Separation Angle (°): 2.70
Uniformity (%): <1
Zero Order, Relative to the Incident Beam (%): <1
Damage Threshold, Reference: See Link for More Details

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant