

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 1064nm, 12.5mm Diameter, Raman Edge Filter



Stock #86-232 ☒ In Stock

- 1 + €505,00

ADD TO CART

Qty 1-9

€505,00

Qty 10+

€420,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.50 +0.0/-0.1

Angle of Incidence (°):  
0 ±2

Optical Density OD (Average):  
≥6.0

|                                                                                                                                                    |
|----------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Cut-On Wavelength (nm):</b><br>1,074.60                                                                                                         |
| <b>Design Wavelength DWL (nm):</b><br>1064                                                                                                         |
| <b>Substrate:</b> <br><a href="#">Fused Silica</a> (Corning 7980) |
| <b>Coating:</b><br>Hard Coated                                                                                                                     |
| <b>Rejection Wavelength (nm):</b><br>831 - 1064                                                                                                    |
| <b>Surface Quality:</b><br>60-40                                                                                                                   |
| <b>Thickness Tolerance (mm):</b><br>+0.1/-0.1                                                                                                      |
| <b>Transmission (%):</b><br>>93                                                                                                                    |
| <b>Type:</b><br>Longpass Filter                                                                                                                    |
| <b>Transition Width (nm):</b><br><10.6                                                                                                             |
| <b>Clear Aperture (%):</b><br>>80                                                                                                                  |
| <b>Durability:</b><br>Environmental: MIL-STD-810F<br>Physical: MIL-C-48497A                                                                        |
| <b>Transmitted Wavefront, RMS:</b><br><λ/4 @ 633nm                                                                                                 |
| <b>Mount Thickness (mm):</b><br>3.5                                                                                                                |
| <b>Note:</b><br>Bandwidth (nm): >900                                                                                                               |
| <b>Coating Specification:</b><br>T <sub>avg</sub> ≥93% @ 1077.8 - 2000nm                                                                           |
| <b>Wavelength Range (nm):</b><br>831 - 1064                                                                                                        |
| <b>Laser Blocking Wavelength (nm):</b><br>1064.00                                                                                                  |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |