

TECHSPEC® 1025nm 12.5mm Dia., High Performance Longpass Filter



High Performance OD 4.0 Longpass Filters

Stock **#86-066** ☒ In Stock



1



€204,00

ADD TO CART

Qty 1-5

€204,00

Qty 6+

€174,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Cut-On Wavelength (nm): 1,025.00
Substrate: Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 200 - 1005
Surface Quality: 60-40
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.1
Transmission (%): ≥91
Transmission Wavelength (nm): 1045 - 1650
Type: Longpass Filter
Clear Aperture (%): >80
Transmitted Wavefront, RMS: ≤λ/4 @ 633nm (prior to coating)
Cut-On Tolerance (%): ±1
Slope Factor (%): <1
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per ML-PRF-13830B, Section C.4.5.12 Moderate abrasion per ML-PRF-13830B, Section C.4.5.11 Cleaning per ML-C-48497A Section 4.5.4.2
Note: Arrow on part indicates filter coated surface.
Coating Specification: Surface 1: Hard Dielectric Sputtered Surface 2: AR Coated
Wavelength Range (nm): 200 - 1650

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant