

[See all 10 Products in Family](#)

# 10.4" Diameter, 9.0" FL, Aspheric Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock **#46-390** **6 In Stock**

-

1

+

€149<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | €149,00 each                  |
| Qty 11-49      | €127,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

| General                          |                               |
|----------------------------------|-------------------------------|
| Fresnel Lens                     | Type:                         |
| Physical & Mechanical Properties |                               |
| 264.16                           | Diameter (mm):                |
| 0.06                             | Center Thickness CT (inches): |

|       |                                 |
|-------|---------------------------------|
| 10.4  | Diameter (inches):              |
| ±0.05 | Dimensional Tolerance (inches): |

|      |                              |
|------|------------------------------|
| 10.0 | Effective Diameter (inches): |
| ±40  | Thickness Tolerance (%):     |

|                    |                                     |
|--------------------|-------------------------------------|
| Optical Properties |                                     |
| 228.60             | Effective Focal Length EFL (mm):    |
| Acrylic            | Substrate: <input type="checkbox"/> |
| Uncoated           | Coating:                            |
| 400 - 1100         | Wavelength Range (nm):              |

|        |                                      |
|--------|--------------------------------------|
| 9.00   | Effective Focal Length EFL (inches): |
| 100.00 | Groove Density (grooves/inch):       |

|              |                                        |
|--------------|----------------------------------------|
| 1.49         | Index of Refraction (n <sub>d</sub> ): |
| 85 (Typical) | Transmission (%):                      |

|                                    |                             |
|------------------------------------|-----------------------------|
| Environmental & Durability Factors |                             |
| 80 (Maximum)                       | Operating Temperature (°C): |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |

|           |            |
|-----------|------------|
| Compliant | Reach 242: |
|-----------|------------|

## Product Details

- Thin, Flat Lenses for Focusing Applications
  - Large Sizes for Maximum Light Collection
  - Aspherically-Grooved Contours for Enhanced Performance
- Aspherically Contoured Fresnel Lenses are thin, flat lenses for focusing applications. A Fresnel lens replaces the curved surface of a conventional lens with a series of concentric grooves, molded into the surface of a thin, lightweight plastic sheet. The grooves act as individual refracting surfaces, like tiny prisms when viewed in cross section, bending parallel rays in a very close approximation to a common focal length. Aspherically Contoured Fresnel Lenses are thin, so very little light is lost by absorption. Fresnel lenses are a compromise between efficiency and image quality. High groove density allows higher quality images, while low groove density yields better efficiency (as needed in light gathering applications). In infinite conjugate systems, the grooved side of the lens should face the longer conjugate.
- Fresnel lenses are most often used in light gathering applications, such as condenser systems or emitter/detector setups. Fresnel lenses can also be used as magnifiers or projection lenses; however, due to the high level of distortion, this is not recommended.

## Technical Information



