

[See all 10 Products in Family](#)

TECHSPEC® 1064nm, 0° 25.4mm Dia. Nd:YAG IBS Low Loss Laser Line Mirror



Stock #89-452 **6 In Stock**

- 1 + €224.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€224,00 each
Qty 6-25	€196,00 each
Qty 26+	€190,40 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<1 **Parallelism (arcmin):**

>90 **Clear Aperture (%):**

Commercial Polish	Back Surface:
25.40 +0.0/-0.1	Diameter (mm):
5.00 ±0.1	Thickness (mm):
Optical Properties	
20-10	Surface Quality:
99.95	Reflection at DWL (%):
>99.95	Reflectivity (Rs%):
>99.95	Reflectivity (Rp%):
>99.5	Reflectivity (Rs% Rp%):
R _s >99.95% @ 1064nm R _p >99.95% @ 1064nm	Coating Specification:
1030 - 1064	Wavelength Range (nm):
λ/8	Surface Flatness (P-V):
Dielectric	Coating Type:
Laser Mirror (1030-1064nm)	Coating:
1064	Design Wavelength DWL (nm):
0	Angle of Incidence (°):
Fused Silica (Coming 7980)	Substrate: <input type="checkbox"/>
>12 J/cm ² @ 1064nm, 10ns	Damage Threshold, By Design: <input type="checkbox"/>

Environmental & Durability Factors

ML-C-675A	Durability:
-----------	--------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Up to 99.98% Reflectivity
- Certified High Laser Damage Threshold at DWL up to 15 J/cm² @ 1064nm
- [Superpolished](#) Substrates Available with Parts per Million Level Scattering Performance
- Additional Sizes Coming Soon

TECHSPEC® High Performance Nd:YAG Laser Line Mirrors are coated using ion beam sputtering (IBS) technology. These laser mirrors are designed for extremely demanding laser applications that require the highest reflection at their design wavelength. The Ion Beam Sputtered coating causes these mirrors to have lower surface roughness than competing coating technologies, resulting in less scatter. TECHSPEC® High Performance Nd:YAG Laser Line Mirrors feature high environmental stability due to dense coating films. Environmental factors such as temperature and humidity cause negligible performance degradation.

Please contact us if your application requires an IBS Laser Line Mirror with custom dimensions or a custom IBS mirror coating.



Superpolished Optics for Minimized Scatter

[Learn More](#) 

Compatible Mounts
