

1064nm, 18mm Dia., 5x5 Spot Matrix, Diffractive Beamsplitter



HOLO/OR Diffractive Beamsplitters

Stock **#14-691** 3-4 DAYS

- 1 + **€1.605,00**

ADD TO CART

Qty 1+
€1.605,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
16.2

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):
18.00 +0.05/-0.15

Substrate:

Fused Silica (Coming 7980)
Thickness (mm): 3.00 ±0.1
Input Beam Mode: SMor MM
Minimum Beam Diameter (mm): 0.18
Overall Efficiency (%): 74
Full Angle (°) : 4.0 x4.0
Output Number of Spots: 5 x5
Separation Angle (°): 1.0 x1.0
Uniformity (%): <8
Zero Order, Relative to the Average (%): 0-100
Damage Threshold, Reference: ☐ See Link for More Details

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant