

1064nm, 25.4mm Dia., 1x6 Spot Array, Diffractive Beamsplitter



HOLO/OR Diffractive Beamsplitters

Stock #14-689 3-4 DAYS

- 1 + **€1.605,00**

ADD TO CART

Qty 1+
€1.605,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
22.9

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):
25.40 +0.05/-0.15

Substrate:

Fused Silica (Coming 7980)	
Thickness (mm):	3.00 ±0.1
Input Beam Mode:	SMor MM
Minimum Beam Diameter (mm):	0.48
Overall Efficiency (%):	82
Full Angle (°) :	3.8
Output Number of Spots:	6
Separation Angle (°):	0.76
Uniformity (%):	<5
Zero Order, Relative to the Incident Beam (%):	<1.5
Damage Threshold, Reference: ☐ See Link for More Details	

Regulatory Compliance

RoHS 2015:	Compliant
Certificate of Conformance:	View
Reach 233:	Compliant