

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

# 1064nm, 8-12mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πSnaper\_1064\_Q-

See More by [AdiOptica](#)



Focal Flat Top Beam Shaper



Stock #12-233 3-4 DAYS

- 1 + €3.040,00

ADD TO CART

Qty 1-4

€3.040,00

Qty 5+

€2.734,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):  
20

|                                                                |
|----------------------------------------------------------------|
| <b>Design Wavelength DWL (nm):</b><br>1064                     |
| <b>Diameter (mm):</b><br>42.00                                 |
| <b>Model Number:</b><br>πShaper_1064_Q-10                      |
| <b>Length (mm):</b><br>29.00                                   |
| <b>Transmission (%):</b><br>>99                                |
| <b>Type:</b><br>Beam Shaper                                    |
| <b>Weight (g):</b><br>50                                       |
| <b>Wavelength Range (nm):</b><br>1020 - 1100                   |
| <b>Input Beam Diameter, 1/e<sup>2</sup> (mm):</b><br>8 - 12    |
| <b>Maximum Input Power, CW (kW):</b><br>0.2                    |
| <b>Inner Thread:</b><br>M30 x 0.75                             |
| <b>Outer Thread:</b><br>M30 x 0.75                             |
| <b>Compatible Adapter:</b><br><a href="#">#12-322</a>          |
| <b>Input Beam Mode:</b><br>TEM <sub>00</sub>                   |
| <b>Typical Input Beam Mode Quality, M<sup>2</sup>:</b><br><1.5 |
| <b>Input Beam Divergence (mrad):</b><br>±20                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |