

LightPath 354260 | 1064nm Alignment, 0.16 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#64-766** CLEARANCE **20+ In Stock**

-

1

+

€60⁷⁵ €121,49

ADD TO CART

Volume Pricing	
Qty 1+	€121,49 €60,75 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

354260Lightpath Lens Code:

Fiber Collimator	Type:
Lens Included:	
#37-100	
Physical & Mechanical Properties	
5.00	Clear Aperture CA (mm):
Protective as needed	Bevel:
304L Stainless Steel Housing	Construction:
11.00	Housing Diameter (mm):
20.2	Housing Length (mm):
Optical Properties	
15.29 @ 780nm	Effective Focal Length EFL (mm):
0.16	Numerical Aperture NA:
D-ZK3	Substrate: ☐
BBAR (1050-1600nm)	Coating:
R _{abs} <1.0% @ 1050 - 1600nm	Coating Specification:
40-20	Surface Quality:
3.13	f#:
1050 - 1600	Wavelength Range (nm):
Infinite	Conjugate Distance:
1064	Alignment Wavelength (nm):
< 0.090	Transmitted Wavefront Error (λ, RMS):
Hardware & Interface Connectivity	
SMA	Connector:
Threading & Mounting	
M11 x0.5	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

PRODUCT DETAILS

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

TECHNICAL INFORMATION

