

**TECHSPEC® 10X, 355nm Vega® Nd:YAG Laser Line Beam Expander**



10X, 355nm DABeam Expander, #35-115

Stock #35-115 3-4 DAYS



1



€495,00

ADD TO CART

Qty 1-9

€495,00

Qty 10+

€436,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):  
0

Coating:  
Laser V-Coat (355nm)

Design Wavelength DWL (nm):  
355

|                                                                                                    |
|----------------------------------------------------------------------------------------------------|
| <b>Entrance Aperture (mm):</b><br>7.5                                                              |
| <b>Exit Aperture (mm):</b><br>26                                                                   |
| <b>Expansion Power:</b><br>10X                                                                     |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)          |
| <b>Length (mm):</b><br>82.60                                                                       |
| <b>Mounting Threads:</b><br>Input: Male M30 x 1<br>Output: Female M34 x 0.5 (not intended for use) |
| <b>Transmission (%):</b><br>>98.5 (nominal)                                                        |
| <b>Type:</b><br>Beam Expander                                                                      |
| <b>Weight (g):</b><br>175                                                                          |
| <b>Housing Diameter (mm):</b><br>39.95                                                             |
| <b>Transmitted Wavefront, P-V:</b><br><λ/10 for 2.3mm input beam (nominal, λ = DWL)                |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 355nm                                   |
| <b>Wavelength Range (nm):</b><br>340 - 380                                                         |
| <b>Style:</b><br>Fixed Magnification                                                               |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>2.5 J/cm² @ 355nm, 10ns, 20Hz      |
| <b>Divergence Adjustment:</b><br>Rotating Optics                                                   |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |