

TECHSPEC® 10mm Dia, 0.67 Numerical Aperture NIR Coated, Aspheric Lens



Stock **#69-860** ☐ In Stock

[Other Coating Options](#)

-

1

+

€200,00

ADD TO CART

Qty 1-5
€200,00

Qty 6+
€160,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
10.00 +0.0/-0.1

Effective Focal Length EFL (mm):
7.50 @ 587.6nm

Numerical Aperture NA:

0.67
Back Focal Length BFL (mm): 4.51
Substrate: N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 9
Edge Thickness ET (mm): 2.21
Center Thickness CT (mm): 5.00 ±0.1
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 133.33

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant