

[See all 215 Products in Family](#)

**TECHSPEC®**

## 10mm Dia., 0.67 Numerical Aperture, 900-1700nm Coated, Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#22-991** [CONTACT US](#)

[Other Coating Options](#)

− 1 + €279<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€279,00 each
Qty 6-10	€251,00 each
Qty 11-25	€229,00 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Aspheric Lens **Type:**

### Physical & Mechanical Properties

**Diameter (mm):**

10.00 +0.00/-0.025

Centering (arcmin):  
<3

Clear Aperture CA (mm):  
9.00

Edge Thickness ET (mm):  
5.25

Center Thickness CT (mm):  
7.50 ±0.10

Bevel:  
Protective as needed

Shape of Back Surface:  
Plano

## Optical Properties

Effective Focal Length EFL (mm):  
7.50 @ 587.6nm

Numerical Aperture NA:  
0.67

Back Focal Length BFL (mm):  
3.35

Substrate:   
[N-SF6](#)

Asphere Figure Error, RMS @ 632.8nm:  
0.4λ

Coating:  
SWIR+ (900-1700nm)

Coating Specification:  
R<sub>avg</sub> <0.5% @ 900 - 1700nm @ ±30° AOI  
R<sub>abs</sub> <1.5% @ 900 - 1700nm @ ±30° AOI

Surface Quality:  
40-20

f/#:  
0.75

Wavelength Range (nm):  
900 - 1700

Conjugate Distance:  
Infinite

Power (diopters):  
133.33

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 250:  
[Compliant](#)

## Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.