


**TECHSPEC® 1.0mm Diameter, LASFN-35 Ball Lens**



Stock #47-128 **20+ In Stock**

€90.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€90,00 each
Qty 11-49	€80,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Ball Lens Type:

**Physical & Mechanical Properties**

1.00 Diameter (mm):

+0/-3 Diameter Tolerance (µm):

## Optical Properties

LASFN-35

Substrate:

Uncoated

Coating:

400 - 2400

Wavelength Range (nm):

2.022

Index of Refraction ( $n_d$ ):

2.00

Sphericity ( $\mu\text{m}$ ):

## Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 247:

## Product Details

- 2.0 Index of Refraction
- High Tolerance
- [High Index Half-Ball Lenses](#) Also Available

TECHSPEC® High Index Ball Lenses provide for a shorter back focal length, simplifying fiber coupling, due to the high index of refraction. Ball lenses are manufactured from a single glass substrate and can either focus or collimate light. The LASFN-35 substrate has an Abbe Number of 29.06, density of 5.41g/cm<sup>3</sup>, and coefficient of linear expansion of 7.4 microns/°K (-30 to 70°C). TECHSPEC® High Index Ball Lenses are ideal for endoscopy, bar code scanning, ball pre-forms for aspheric lenses, and sensor applications.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts