

**TECHSPEC® 10mm Dia. x 40mm FL, VIS 0° Coated, Achromatic Lens**



Stock **#63-709** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€74,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €74,00                        |
| Qty 6+                        |
| €59,25                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
10.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                                                                                                                 |
|-------------------------------------------------------------------------------------------------------------------------------------------------|
| 40.00                                                                                                                                           |
| Focal Length Tolerance (%):<br>±1                                                                                                               |
| Back Focal Length BFL (mm):<br>37.79                                                                                                            |
| Focal Length Specification Wavelength (nm):<br>587.6                                                                                            |
| Clear Aperture CA (mm):<br>9.00                                                                                                                 |
| Centering (arcmin):<br><1                                                                                                                       |
| Center Thickness CT (mm):<br>4.50 ±0.10                                                                                                         |
| Center Thickness CT 1 (mm):<br>3.00 ±0.05                                                                                                       |
| Center Thickness CT 2 (mm):<br>1.50 ±0.05                                                                                                       |
| Radius R <sub>1</sub> (mm):<br>23.66                                                                                                            |
| Radius R <sub>2</sub> (mm):<br>-18.11                                                                                                           |
| Radius R <sub>3</sub> (mm):<br>-55.78                                                                                                           |
| Edge Thickness ET (mm):<br>3.74                                                                                                                 |
| Substrate: <br><a href="#">N-BK7</a> / <a href="#">N-SF5</a> |
| Surface Quality:<br>40-20                                                                                                                       |
| f/#:<br>4.00                                                                                                                                    |
| Numerical Aperture NA:<br>0.13                                                                                                                  |
| Coating:<br>VIS 0° (425-675nm)                                                                                                                  |
| Coating Specification:<br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                                                                                  |
| Power (P-V) @ 632.8nm:<br>1.5λ                                                                                                                  |
| Irregularity (P-V) @ 632.8nm:<br>λ/4                                                                                                            |
| Bevel:<br>Protective bevel as needed                                                                                                            |
| Type:<br>Achromatic Lens                                                                                                                        |
| Wavelength Range (nm):<br>425 - 675                                                                                                             |

### Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Compliant</a>             |
| Reach 219:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |