

[All Products](#) / [Optics](#) / [Polarization](#)
/ [Absorptive \(Dichroic\) Polarizers](#)
/ [Commercial Grade NIR Polarizers](#)


[See all 13 Products in Family](#)

10mm Dia. XP-NIR

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region: European Union

Submit



Stock #73-337 **20+ In Stock**

1

€25^{,50}

ADD TO CART

Volume Pricing	
Qty 1-10	€25,50 each
Qty 11-25	€20,40 each
Qty 26-49	€17,90 each
Need More?	Request Quote

Product Downloads
EO Spec Sheet

Prices shown are exclusive of VAT/local taxes

General

Type: Linear Polarizer

Note: Delivered with protective film on both sides
Polarization axis indicated by notch cut into edge (circular parts) or stripe on protective film
Pressure Sensitive Adhesive (PSA) on one side

Physical & Mechanical Properties

Diameter (mm): 10.00 +0/-0.3

Thickness (mm): 0.21 +/- 0.025

Construction: Polarizing Film

Optical Properties

Coating: Uncoated

Extinction Ratio: >160:1 from 800-1000nm (Average, Typical)

Substrate: XP-NIR Polarizing Film

Wavelength Range (nm): 800 - 1000

Polarization Efficiency (%): >99.0 @ 860nm

Transmission, Single (%): 35 +/- 3.0 @860nm

Environmental & Durability Factors

Heat Resistance (°C x Hours): 105C x 500h (dry) Change in single

Cold Resistance (°C x Hours): -40C x 1000h Change in single transmittance @

transmittance @ 870nm <+/-5%
60C x 1000h (90% humidity)
Change in single transmittance @ 870nm <+/-5% from initial value, change in polarization efficiency @ 870nm <-3% from initial value

870nm <+/-5% from initial value
Change in polarization efficiency @ 870nm <-3% from initial value

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: [View](#)

Reach 250: **Compliant**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Optimized Performance Between 800-1000nm
- Ideal for Sensing and Inspection Applications
- Available in Sizes up to 600 x 900mm
- **Near-Infrared (NIR) Linear Polarizing Film** and **High Contrast Near-Infrared (NIR) Polarizing Film** also Available for Broadband IR Applications

Commercial Grade NIR Polarizing Film (XP-NIR) offers a cost-effective solution for polarization applications in the 800-1000nm range. This film offers contrast ratios of >160:1 (Average) and >99% polarization efficiency in the specified range, and its high environmental resistance makes it a great choice for demanding environments. Commercial Grade NIR Polarizing Film (XP-NIR) is delivered with a pressure sensitive adhesive (PSA) on one side and is available in circular or rectangular sizes, with up to a 50mm diameter or a 600 x 900mm format. This film is ideal for commercial sensing, inspection, and LIDAR applications.

Note: Custom sizes available up to 1000mm

Technical Information


Related Products




Optomechanics for Polarizers



NIR Glass Linear Polarizers



Wire Grid Polarizing Film



Corning Polarcor™ Glass Polarizers


Frequently Purchased Together




#34-475 - 50mm Dia. White Diffusing Glass
€45,25

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:



#35-275 - Disc (0.25" Diameter x 0.2" Thickness) Package of 2, SmCo mixed
€15,50

#48-333 - 6.0mm Dia. x -9 FL, Uncoated, Plano-Concave Lens
€31,75

#48-678 - 6.0mm Dia. x -15 FL, Uncoated, Plano-Concave Lens
€31,75

Resources

Media Type

Glossary

