


In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 10mm Sq., 1mm Thick, MgF<sub>2</sub> Coated λ/4 N-BK7 Window



Stock #23-369 3-4 DAYS



1



€65,50

ADD TO CART

Qty 1-5

€65,50

Qty 6+

€52,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v<sub>d</sub>):  
64.17

Bevel:  
Protective as needed

Clear Aperture (%):  
90

|                                                                                                                |
|----------------------------------------------------------------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>9.00 x 9.00                                                                  |
| <b>Dimensions (mm):</b><br>10.00 x 10.00 +0.00/-0.25                                                           |
| <b>Thickness (mm):</b><br>1.00 ±0.20                                                                           |
| <b>Coating:</b><br>MgF <sub>2</sub> (400-700nm)                                                                |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤1.75% @400 - 700nm                                          |
| <b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b><br>7.1 (-30 to +70°C)<br>8.3 (+20 to +300°C) |
| <b>Density (g/cm³):</b><br>2.51                                                                                |
| <b>Edges:</b><br>Fine Ground                                                                                   |
| <b>Index of Refraction n<sub>d</sub>:</b><br>1.516                                                             |
| <b>Knoop Hardness (kg/mm²):</b><br>610                                                                         |
| <b>Parallelism (arcmin):</b><br><1                                                                             |
| <b>Poisson's Ratio:</b><br>0.206                                                                               |
| <b>Substrate:</b><br><a href="#">N-BK7</a>                                                                     |
| <b>Surface Quality:</b><br>60-40                                                                               |
| <b>Transmitted Wavefront, P-V:</b><br>λ/4                                                                      |
| <b>Type:</b><br>Protective Window                                                                              |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                                     |
| <b>Young's Modulus (GPa):</b><br>82                                                                            |
| <b>Length (mm):</b><br>10.00                                                                                   |
| <b>Width (mm):</b><br>10.00                                                                                    |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>10 J/cm² @532nm, 10ns                          |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |