

[See all 21 Products in Family](#)

## 12-50mm FL, CS-Mount, P-iris, 4K Motorized Zoom, Focus, Iris & IRC w/Limit Switch



Image represents #22-806: Design will vary by stock number.

Stock **#22-814** **2 In Stock**

⊖ 1 ⊕ €626<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€626,00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

### General

**Note:**  
User with Motorized Lens Control Board (#22-830)

**Type:**  
Varifocal Lens

### Physical & Mechanical Properties

**Iris Option:**  
P-iris

52.00	Length (mm):
61.0	Maximum Diameter (mm):
68	Weight (g):

## Optical Properties

36° - 8.6°	Horizontal Field of View @ Max Sensor Format:
12-50	Focal Length Range (mm):
2000 - ∞	Working Distance (mm):
f/1.8- Closed	Aperture (f#):
VS	Lens Wavelength Range:

## Sensor

1/1.7"	Maximum Sensor Format:
--------	------------------------

## Threading & Mounting

CS-Mount	Mount:
----------	--------

## Regulatory Compliance

<a href="#">View</a>	Certificate of Conformance:
----------------------	-----------------------------

## Product Details

- 4 - 10mm Focal Length Range for up to 135° Horizontal FOV
- True 4K, 12 Megapixel Resolution
- IR corrected for Day or Night

4K Wide Angle Lenses provide a wide range of fields of view for applications with long working distance requirements, allowing for excellent resolution up to 12 megapixels. Available with DC auto-iris, P-iris, and manual iris versions, these lenses are ideal for a wide range of applications including Intelligent Traffic (ITS), remote sensing, security, and robotics. The lenses are IR corrected for use with true DayNight cameras, providing a bright image in both visible and IR illumination without manual adjustment. Lens mounting options include S-mount (M12), CS-mount, and C-mount with motorized and non-motorized versions available.