

## 12 x 12mm, 500µm Pitch, 2.3° Div., Cyl. Microlens Array UV-VIS



Stock #72-603 **1 In Stock**

⊖ 1 ⊕ €608.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€608,00 each
Qty 11+	€485,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Lens Array

Type:

### Physical & Mechanical Properties

12.0 x 12.0 ±0.10

Dimensions (mm):

5.500

Radius R (mm):

2.00 ±0.10 **Thickness (mm):**

## Optical Properties

**Effective Focal Length EFL (mm):**  
12.20 @ 1064nm

**Substrate:**   
[Fused Silica](#) (Corning 7980)

**Coating:**  
UV-NIR (250-700nm)

**Wavelength Range (nm):**  
250 - 700

**Coating Specification:**  
R<sub>abs</sub> ≤ 1.0% from 350 - 450nm @ 0° AOI  
R<sub>avg</sub> ≤ 1.5% @ 250 - 700nm @ 0°

**Divergence Angle (°):**  
2.3 (Full Width)

**Pitch (µm):**  
500.00

**Array Type:**  
Single-Sided

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 250:**  
[Compliant](#)

## Product Details

- Generate Non-Gaussian Line Patterns
- Ideal for Light Homogenization
- Excellent Performance from 193nm – 2.5µm

Cylindrical Microlens Arrays are used to homogenize a variety of light sources, including lasers or high power LEDs. Unlike [Square Microlens Arrays](#), which generate spot patterns, Cylindrical Microlens Arrays yield non-gaussian line patterns, and are ideal for welding, drilling, or laser ablation applications from the UV to IR. Cylindrical Microlens Arrays are available uncoated, VIS-NIR, or UV-NIR coated, including options with lenses on a single side for line generation applications or double-sided (with cross-oriented lenses) for beam homogenisation. Additionally, these lenses can be used as fast axis collimators.