

TECHSPEC® 12.0mm Dia. x 24.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#31-855** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€35,00**

ADD TO CART

Qty 1-9
€35,00
Qty 10+
€31,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

24.00 @ 587.6nm
Back Focal Length BFL (mm): 22.15
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.80 ± 0.05
Edge Thickness ET (mm): 1.25
Radius R ₁ (mm): 12.42
Clear Aperture CA (mm): 11
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, Reference: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View