


TECHSPEC® 12.5mm 980nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-881** CLEARANCE 3-4 DAYS

-

1

+

€100.⁰⁰

ADD TO CART

Qty 1+

€100,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Linear Polarizer

Physical & Mechanical Properties

Protective bevel as needed	Bevel:
90.00	Clear Aperture (%):
Cube	Construction:
12.5 x 12.5 x 12.5 ±0.1	Dimensions (mm):
Optical Properties	
±3	Beam Deviation (arcmin):
R _{abs} <0.25% @ 980nm	Coating Specification:
980	Design Wavelength DWL (nm):
1000:1	Extinction Ratio:
>90	P-Polarization Transmission (%):
>99.5	S-Polarization Reflection (%):
N-BK7	Substrate: ☐
40-20	Surface Quality:
1.25	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Regulatory Compliance	
Compliant	RoHS:
View	Certificate of Conformance:

PRODUCT DETAILS

- Designed for Common Diode, Gas, and Solid State Lasers
 - Reflects S-Polarized Light, Transmits P-Polarized Light
 - High Extinction Ratio
- TECHSPEC® Laser Line Polarizing Cube Beamsplitters split randomly polarized beams into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. The beamsplitters consist of a pair of precision [right angle prisms](#) cemented together to minimize transmitted wavefront distortion, and to provide excellent parallelism between incoming and transmitted beams. TECHSPEC® Laser Line Polarizing Cube Beamsplitters are designed for many common laser wavelengths and have a high extinction ratio. These beamsplitters are designed for common diode, gas, and solid-state laser applications.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

TECHNICAL INFORMATION

