

TECHSPEC® 12.5mm Dia 0.50 NA, VIS Coated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#87-988** 3-4 DAYS

[Other Coating Options](#)

− 1 +

€395,00

ADD TO CART

Qty 1-5

€395,00

Qty 6+

€316,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Effective Focal Length EFL (mm): 12.50 @ 587.6nm
Numerical Aperture NA: 0.50
Back Focal Length BFL (mm): 8.39
Substrate:  Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: VS (425-675nm)
Coating Specification: R _{avg} <1.5% @ 425 - 675nm
Centering (arcmin): ≤5
Surface Quality: 60–40
Clear Aperture CA (mm): 11
Edge Thickness ET (mm): 1.98
Center Thickness CT (mm): 6.00 ±0.1
f/#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 425 - 675
Conjugate Distance: Infinite
Power (diopters): 80.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant