

[See all 130 Products in Family](#)

TECHSPEC[®] 12.5mm Dia. 1064nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC[®] Nd:YAG Laser Line Mirrors



Stock **#45-986** 20+ In Stock

-

1

+

€126^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€126,00 each
Qty 6-25	€109,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Laser Mirror

Physical & Mechanical Properties

Parallelism (arcmin):

<3

>90	Clear Aperture (%):
Ground	Back Surface:
12.50 +0.00/-0.20	Diameter (mm):
6.00 ±0.20	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
99.8	Reflection at DWL (%):
Coating Specification: R _{abs} >99.8% @ 1064nm @ 45° AOI R _{avg} >99.5% @ 1046 - 1074nm @ 45° AOI	
1046 - 1074	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Dielectric	Coating Type:
Laser Mirror (1064nm)	Coating:
1064	Design Wavelength DWL (nm):
45	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: □
20 J/cm2 @ 1064nm, 20ns, 20Hz	Damage Threshold, Reference: □

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
 - High Laser Induced Damage Threshold Specifications
 - 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
 - TECHSPEC® Laser Mirror Substrates and TECHSPEC® Yb:YAG Laser Line Mirrors Also Available
- TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts