

TECHSPEC® 12.5mm Dia. 266nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#88-523** 3-4 DAYS



1



€144,00

ADD TO CART

Qty 1-5

€144,00

Qty 6+

€127,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) :>90
Back Surface: Ground
Reflection at DWL (%) : 99.9
Coating Specification: R _{abs} >99.8% @ 266nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (266nm)
Design Wavelength DWL (nm): 266
Diameter (mm): 12.50 +0.0/-0.2
Thickness (mm): 6.00 ±0.2
Angle of Incidence (°): 0-45
Substrate: ▢ Fused Silica (Corning 7980)
Damage Threshold, Reference: ▢ 2.0 J/cm² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View