

TECHSPEC® 12.5mm Dia 1550nm 45°, Laser Diode Mirror



Stock **#63-156** 3-4 DAYS

⊖ 1 ⊕ **€116,00**

ADD TO CART

Qty 1+
€116,00

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality: 10-5
Type: Laser Mirror
Parallelism (arcmin): <3
Clear Aperture (%): >90

Back Surface: Ground
Reflection at DWL (%): 99.8
Coating Specification: R _{abs} >99.8% @ 1550nm R _{avg} >98% @ 1440 - 1660nm
Wavelength Range (nm): 1440 - 1660
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Dielectric Mirror (1440-1660nm)
Design Wavelength DWL (nm): 1550
Diameter (mm): 12.50 +0.0/-0.2
Thickness (mm): 6.00 ±0.2
Angle of Incidence (°): 45
Substrate: ☐ Fused Silica (Corning 7980)

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View