

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.5mm Dia. 1" Nom. Fused Silica Wedge Prism 355nm Laser V-Coat



TECHSPEC Fused Silica Wedge Prisms

Stock #39-074 CLEARANCE 3-4 DAYS



1



€94,95

ADD TO CART

Qty 1+

€94,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Laser V-Coat (355nm)

Angle Tolerance (arcsec):
30

Bevel:
Protective bevel as needed

Coating Specification:
R_{abs} <0.25% @ 355nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52
Design Wavelength DWL (nm): 355
Diameter (mm): 12.50
Image Orientation: Beam Deviation
Power (diopters): 1.74
Ray Deviation @ 355nm (°): 1.00
Substrate: Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Wedge Angle: 2° 5'56"
Damage Threshold, By Design: 7.5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View