

TECHSPEC® 12.5mm Dia. x 100mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-333-INK** [CONTACT US](#)

[Other Coating Options](#)

- 1 + **€96,00**

ADD TO CART

Qty 1-5
€96,00
Qty 6+
€76,75
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):

100.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 97.92
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.50
Centering (arcmin) : <1
Center Thickness CT (mm) : 4.50 ±0.10
Center Thickness CT 1 (mm) : 3.00 ±0.05
Center Thickness CT 2 (mm) : 1.50 ±0.05
Radius R₁ (mm) : 61.54
Radius R₂ (mm) : -44.39
Radius R₃ (mm) : -130.26
Edge Thickness ET (mm) : 4.03
Substrate: ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 8.00
Numerical Aperture NA : 0.06
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View