

TECHSPEC® 12.5mm Dia., 3.00mm Thick, 532nm, λ/10 Fused Silica Window



TECHSPEC λ/10 Laser Line Coated Windows

Stock **#48-208** ☒ In Stock

⊖ 1 ⊕ **€132,50**

ADD TO CART

Qty 1-5

€132,50

Qty 6+

€106,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
11.25

Coating:
Laser V-Coat (532nm)

Design Wavelength DWL (nm): 532
Diameter (mm): 12.50 +0.00/-0.10
Substrate: Fused Silica Excimer Grade (Coming 7980 KrF)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Type: Laser Line Window
Bevel: Protective as needed
Clear Aperture (%): 90
Transmitted Wavefront, P-V: λ/10
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤5
Coating Specification: R_{abs} <0.25% @ 532nm
Damage Threshold, By Design: 10 J/cm² @ 532nm, 20ns, 20Hz
Fused Silica Grade: 7980 KrF 0A
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View