

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12.5mm Dia. x 15mm FL, VIS 0⁺ Coated, Achromatic Lens



Stock #63-712 ☐ In Stock
[Other Coating Options](#)

1 €81,00

ADD TO CART

Qty 1-5
€81,00
Qty 6+
€64,75
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):

15.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 10.82
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 7.00 ±0.10
Center Thickness CT 1 (mm): 6.00 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R ₁ (mm): 9.55
Radius R ₂ (mm): -8.60
Radius R ₃ (mm): -48.50
Edge Thickness ET (mm): 4.27
Substrate:  N-LAK22 / N-SF6
Surface Quality: 40-20
f/#: 1.2
Numerical Aperture NA: 0.42
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View