

[See all 18 Products in Family](#)

TECHSPEC® 12.5mm Dia. x 50mm EFL, UV-VIS Coated, Near UV Achromatic Lens



Stock #65-974 **20+ In Stock**

⊖ 1 ⊕ €156⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | €156,00 each |
| Qty 6-25 | €125,00 each |
| Qty 26-49 | €118,00 each |
| Need More? | Request Quote |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

Diameter (mm):

12.50 +0.0/-0.025

11.50 **Clear Aperture CA (mm):**

<1 **Centering (arcmin):**

5.50 ±0.20 **Center Thickness CT (mm):**

3.50 ±0.10 **Center Thickness CT 1 (mm):**

2.00 ±0.10 **Center Thickness CT 2 (mm):**

4.55 **Edge Thickness ET (mm):**

Protective as needed **Bevel:**

Optical Properties

50.00 **Effective Focal Length EFL (mm):**

±1 **Focal Length Tolerance (%):**

47.31 **Back Focal Length BFL (mm):**

405.00 **Focal Length Specification Wavelength (nm):**

29.11 **Radius R₁ (mm):**

-25.27 **Radius R₂ (mm):**

-71.39 **Radius R₃ (mm):**

Substrate:
N-FK5 / F2HT

40-20 **Surface Quality:**

4 **f#:**

0.13 **Numerical Aperture NA:**

UV-VIS (345-700nm) **Coating:**

R_{avg} ≤1.5% @ 345 - 700nm **Coating Specification:**

1.5λ **Power (P-V) @ 632.8nm:**

M4 **Irregularity (P-V) @ 632.8nm:**

345 - 700 **Wavelength Range (nm):**

Regulatory Compliance

RoHS 2015:
Exempt

Certificate of Conformance:
View

Reach 235:
Compliant

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).



Product Details

- Excellent Transmission in 345 – 700nm Range

- Ideal for use with NUVLEDs and Mercury Lamps
- Low-Cost, Cemented Design

TECHSPEC® Near-UV (NUV) Achromatic Lenses are specifically designed to minimize the spot size for polychromatic illumination in the 345 – 700nm region. The achromatic lenses are ideal for use in fluorescence applications, as well as for simple focusing of common UV light sources, such as Mercury Arc Lamps, UVLEDs, and Tripled Nd:YAG lasers. Featuring a simple cemented design, the lenses are an excellent alternative to air-spaced doublets and triplets for the UV. TECHSPEC® Near-UV (NUV) Achromatic Lenses feature >90% transmission at 360nm and provide >50% transmission at 334nm. The lenses feature either N-FK5 or F2HT substrate and a UV-MS coating.

Technical Information



Compatible Mounts