

TECHSPEC[®] 12.5mm Dia x 20mm EFL Hastings Triplet Achromatic Lens



Stock **#45-251** 20+ In Stock

-

1

+

€130^{,81}

ADD TO CART

Volume Pricing	
Qty 1-5	€130,81 each
Qty 6-25	€105,06 each
Qty 26-49	€101,97 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General


Type:
Achromatic Triplet Lens

Physical & Mechanical Properties	
12.50 +0.0/-0.025	Diameter (mm):
<3	Centering (arcmin):
10.18	Center Thickness CT (mm):
7.98	Center Thickness A (mm):
1.10	Center Thickness B (mm):
-14.95	Radius R ₄ (mm):
7.44	Edge Thickness ET (mm):
Protective as needed	Bevel:
Optical Properties	
20.00	Effective Focal Length EFL (mm):
±2	Focal Length Tolerance (%):
16.31	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
14.95	Radius R ₁ (mm):
7.34	Radius R ₂ (mm):
-7.34	Radius R ₃ (mm):
N-F2 / N-BK7 / N-F2	Substrate:
40-20	Surface Quality:
1.6	f/#:
0.31	Numerical Aperture NA:
MgF ₂ (400-700nm)	Coating:
R _{avg} ≤1.75% @ 400 - 700nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
400 - 700	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

PRODUCT DETAILS

- Unique, 3-Element Design
 - MgF₂ Coated
 - Steinheil Triplet Achromatic Lenses also Available
- TECHSPEC® Hastings Triplet Achromatic Lenses feature a unique, three-element design that provides distortion free, color-correct viewing. These lenses are computer designed to interact with each other, contributing to the reduction or elimination of “pincushion” distortion, in addition to chromatic and spherical aberrations. TECHSPEC® Hastings Triplet Achromatic Lenses are composed of two concave meniscus elements cemented to a double-convex lens. These lenses are AR coated with MgF₂, making them ideal for performance in the VIS range.

TECHNICAL INFORMATION



COATING CURVES

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS