

TECHSPEC® 12.5mm Dia. x 40mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#32-315** ☐ In Stock

[Other Coating Options](#)

1 **€76,00**

ADD TO CART

Qty 1-5
€76,00

Qty 6+
€60,75

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm): 40.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 37.54
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 5.06 ±0.10
Center Thickness CT 1 (mm): 3.73 ±0.05
Center Thickness CT 2 (mm): 1.33 ±0.05
Radius R₁ (mm): 24.77
Radius R₂ (mm): -18.01
Radius R₃ (mm): -51.17
Edge Thickness ET (mm): 3.88
Substrate: N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 3.2
Numerical Aperture NA: 0.16
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View