

TECHSPEC®

12.5mm Diameter x 1.1mm Thickness, Uncoated, BOROFLOAT® Window

See More by [SCHOTT Optical Components](#)



TECHSPEC BOROFLOAT Borosilicate Windows

Stock **#39-272** **3 In Stock**

-

1

+

€25^{,25}

ADD TO CART

Volume Pricing	
Qty 1-5	€25,25 each
Qty 6-25	€20,00 each
Qty 26-99	€18,00 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window

Type:

Physical & Mechanical Properties

Protective as needed

Bevel:

≥90	Clear Aperture (%):
11.25	Clear Aperture CA (mm):
12.50 ±0.5	Diameter (mm):
1.10 ±0.2	Thickness (mm):
Ground	Edges:
480.00	Knoop Hardness (kg/mm²):
0.20	Poisson's Ratio:
64	Young's Modulus (GPa):

Optical Properties

65.41	Abbe Number (v _d):
Uncoated	Coating:
1.472	Index of Refraction (n _d):
BOROFLOAT®	Substrate:
4 - 6λ	Surface Flatness (P-V):
80-50	Surface Quality:
90	Transmission (%):
350 - 2000	Wavelength Range (nm):

Material Properties

3.25 (+20 to +300°C)	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.23	Density (g/cm³):
525	Transformation Temperature (°C):

Environmental & Durability Factors

1 hour @ 500; >100 hours @ 450	Operating Temperature (°C):
Short Term, 1 hr: 110K 1 - 100 hrs: 90K Long Term, >100 hrs: 80K	Resistance to Temperature Difference (K):
Up to 4mm Thick: 175K 4 - 6mm Thick: 160K 6 - 15mm Thick: 150K	Thermal Shock (K):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


Product Details

- Low Coefficient of Thermal Expansion
- Visible to Near Infrared Transmission
- High Resistance to Thermal Shock

TECHSPEC® BOROFLOAT® Borosilicate Windows are ideal for high temperature and harsh environment applications. The windows have a low coefficient of thermal expansion of 3.25 (+20 to +300°C). TECHSPEC® BOROFLOAT® Borosilicate Windows feature visible to near infrared transmission. Unlike common borosilicate that is drawn flat, BOROFLOAT® is produced by a float technique that yields superior surface flatness —typically 4 - 6λ per inch. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass.

Can't find what you need? Get a quick [custom quote](#).

Technical Information



Quote Your Size

Compatible Mounts

