

TECHSPEC<sup>®</sup>

12.5mm H x 25mm L x -25mm FL MgF<sub>2</sub> Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC<sup>®</sup> Illumination Grade PCV Cylinder Lenses

Stock **#68-072** [CONTACT US](#)

-

 1 

+

 €66<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | €66,00 each                   |
| Qty 6-25       | €60,00 each                   |
| Qty 26-49      | €57,00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Cylinder Lens, Plano-Concave

Type:

Physical & Mechanical Properties

2.50 Center Thickness CT (mm):

|             |                                  |
|-------------|----------------------------------|
| ±0.1        | Center Thickness Tolerance (mm): |
| +0.0/-0.2   | Dimensional Tolerance (mm):      |
| 12.5 x 25.0 | Dimensions (mm):                 |
| 3.95        | Edge Thickness ET (mm):          |

|                                       |                                                       |
|---------------------------------------|-------------------------------------------------------|
| Optical Properties                    |                                                       |
| -25.00                                | Effective Focal Length EFL (mm):                      |
| N-BK7                                 | Substrate: <input type="checkbox"/>                   |
| MgF <sub>2</sub> (400-700nm)          | Coating:                                              |
| 400 - 700                             | Wavelength Range (nm):                                |
| -26.65                                | Back Focal Length BFL (mm):                           |
| R <sub>avg</sub> ≤1.75% @ 400 - 700nm | Coating Specification:                                |
| ±3                                    | Focal Length Tolerance (%):                           |
| -12.92                                | Radius R <sub>1</sub> (mm):                           |
| 60-40                                 | Surface Quality:                                      |
| 10 J/cm <sup>2</sup> @ 532nm, 10ns    | Damage Threshold, By Design: <input type="checkbox"/> |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 235:                  |

## Product Details

• Cylinder Lenses Ideal for 1 Dimensional Laser Beam Convergence


• Circular and Rectangular Form Factors

• Multiple Coating Options Available

TECHSPEC® Illumination Grade PCV Cylinder Lenses are commonly used to turn a collimated laser source into a line generator. These PCV Cylinder Lenses and [TECHSPEC Illumination Grade PCX Cylinder Lenses](#) can be used together for beam expander applications.

The thin lens approximation for the length of a line generated by a negative cylinder lens is:  $L = 2 * (r_0/f) * (z + f)$  where L is the line length,  $r_0$  is half the beam diameter, z is the projection distance, and -f is the focal length of the lens.

## Technical Information



## Coating Curves

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more

- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---