

12.7mm Dia., 532nm, $\lambda/2$ High Energy Waveplate



High Energy Quartz Waveplates

Stock **#25-449** **4 In Stock**

-

1

+

€499⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€499,00 each
Qty 11+	€411,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

High Energy Waveplate

Type:

Physical & Mechanical Properties

8.0	Clear Aperture CA (mm):
12.70	Diameter (mm):
+0/-0.2	Dimensional Tolerance (mm):
Optically Bonded on UVFS (C7980) Substrate	Construction:
<3	Parallelism (arcsec):
Optical Properties	
R _{avg} <0.3%	Coating:
532	Design Wavelength DWL (nm):
Crystalline Quartz	Substrate: ☐
<i>N</i> 2	Retardance:
20-10	Surface Quality:
< <i>N</i> 10 @ 632.8nm	Transmitted Wavefront, P-V:
<i>N</i> 250 @ 20°C	Retardance Tolerance:
>20 J/cm ² @ 1064nm, 10ns, 10Hz	Damage Threshold, By Design: ☐
0	Retardance Order:
Threading & Mounting	
6 ±0.2	Mount Thickness (mm):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Damage Threshold up to >20 J/cm² @ 1064nm
- N*4 and *N*2 Retardance
- Black Anodized Aluminum Mount
- UV to NIR Design Wavelengths Available

High Energy Quartz Waveplates are available in both *N*4 and *N*2 retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm² at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.