

[See all 1 Products in Family](#)

12.7mm Dia. UHR Broadband Dielectric Mirror, 400-750nm



Stock #17-500 CLEARANCE 20+ In Stock

€251⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€251,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror Type:

Physical & Mechanical Properties

12.70 +0.00/-0.10 Diameter (mm):

6.35 ±0.20 Thickness (mm):

11.7 Clear Aperture CA (mm):

Ground

Edges:

Parallelism (arcmin):

<3

Optical Properties

Dielectric

Coating Type:

UHR Dielectric Mirror (400-750nm)

Coating:

M10

Surface Flatness (P-V):

400 - 750

Wavelength Range (nm):

[Fused Silica](#) (Corning 7980)

Substrate:

45

Angle of Incidence (°):

Coating Specification:
R_{avg} >99.9% @ 400 - 750nm (45°, s-pol)
R_{avg} >99.8% @ 410 - 750nm (45°, p-pol)

Surface Quality:

10-5

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- >99.8% Reflectivity over Broad Visible or NIR Wavelength Ranges
- 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
- M10 Surface Flatness

Ultra-High Reflectivity (UHR) Broadband Dielectric Mirrors are ideal for use with broadband [laser](#) or [illumination](#) sources in applications that require low reflection loss. These mirrors feature laser grade substrates with M10 surface flatness and 10-5 surface quality to minimize scattering effects. Coated with durable dielectric coatings, these mirrors are designed for >99.8% average reflectivity throughout the visible (400 - 750nm) or NIR (740 - 1100nm) spectra, independent of polarization. With a high-quality fused silica substrate, Ultra-High Reflectivity (UHR) Broadband Dielectric Mirrors feature a low coefficient of thermal expansion.

Coating Note: Coating designs measured and verified at 532, 632.8, and 1064nm via cavity ring-down spectroscopy (CRDS). Specs may not be verifiable on traditional spectrophotometer equipment.

Technical Information

