

## 12.7mm Dia. 532nm $\lambda/2$ Quartz Waveplate Multiple Order



Stock **#85-084** 3-4 DAYS

- 1 + **€257,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €257,00                       |
| Qty 6+                        |
| €208,00                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):  
8.00

Coating:  
Laser V-Coat (532nm)

Design Wavelength DWL (nm):  
532

Diameter (mm):

|                                                                              |
|------------------------------------------------------------------------------|
| 12.70 +0.00/-0.25                                                            |
| <b>Substrate:</b> <div>Crystal Quartz</div>                                  |
| <b>Retardance:</b><br>λ/2                                                    |
| <b>Surface Quality:</b><br>10-5                                              |
| <b>Thickness (mm):</b><br>6.40 +0.00/-0.25                                   |
| <b>Type:</b><br>Crystalline Waveplate                                        |
| <b>Construction:</b><br>Crystalline                                          |
| <b>Transmitted Wavefront, P-V:</b><br>λ/10 for central 80% of clear aperture |
| <b>Parallelism (arcsec):</b><br><3                                           |
| <b>Retardance Tolerance:</b><br>±λ/200                                       |
| <b>Temperature Coefficient (λ/°C):</b><br>0.0015                             |
| <b>Retardance Order:</b><br>Multiple Order                                   |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |