

[See all 26 Products in Family](#)

TECHSPEC® 12.7mm Dia., 6.35mm Thick, N-BK7 Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock #38-055 **15 In Stock**

⊖ 1 ⊕ €126⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€126,00 each
Qty 6-25	€115,00 each
Qty 26-49	€104,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Window Substrate **Type:**
Glass **Type of Window:**

Physical & Mechanical Properties

Thickness (mm):

6.35 ±0.20

Clear Aperture CA (mm):

11.43

Diameter (mm):

12.70 +0.00/-0.10

Clear Aperture (%):

90

Parallelism (arcmin):

<3

Bevel:

Protective as needed

Edges:

Fine Ground

Optical Properties

Substrate:

N-BK7

Index of Refraction (n_d):

1.516

Surface Quality:

10-5

Coating:

Uncoated

Abbe Number (v_d):

64.17

Wavelength Range (nm):

350 - 2200

Surface Flatness (P-V):

$\lambda/10$

Regulatory Compliance

Certificate of Conformance:

[View](#)

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Up to 10-5 Surface Quality and $\lambda/10$ Surface Flatness Available
- Fused Silica or N-BK7 Material
- Standard Imperial Sizes for Drop-in Replacement Solutions
- [Laser Line Coated Versions](#) Available
- [Mirror Substrates](#) Also Available

TECHSPEC® Uncoated Laser Window Substrates are laser quality window substrates designed to be used in demanding laser applications. These laser window substrates are available, manufactured from fused silica for high power laser applications that require excellent thermal stability or from N-BK7 for more cost sensitive laser applications. Both the fused silica and N-BK7 laser window substrates feature precision grade $\lambda/10$ surface flatness and 10-5 surface quality, ensuring minimal disturbance to transmitted beams. TECHSPEC® Uncoated Laser Window Substrates are available in standard imperial sizes from 12.7 to 50.8mm in diameter for the convenience of drop-in replacement into existing laser systems. Custom dimensional and coating options are available, please contact us for custom inquiries.

Compatible Mounts